



额定电流：2.0A
额定电压：12V
耐电压：500V
接触电阻：30mΩ 以内
绝缘电阻：500MΩ
工作温度：-40℃～+85℃
塑件（材质）：LCP
接触点（材质）：磷铜，触点镀金3U"

RECOMMENDED PCB LAYOUT

TOP VIEW (.XX $\pm$ 0.05)

PART NO.	DIM A	DIM B
HYCW-BA6P2524D-135	2.4	4.30 ± 0.2
HYCW-BA6P2530D-135	3.0	4.90 ± 0.2
HYCW-BA6P2535D-135	3.5	5.40 ± 0.2



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY :	DATE :	PART NAME:	
X.X ±0.30		陈一鸣	2014-02-23	2.5PH 6P 正压电池座 13.5柱	
X.XX ±0.25					
X.XXX ±0.15					
X: ±2° X.X ±0.5°		CHECKED BY:	DATE :	PART NO.	SEE TABLE
		马跃	2014-02-23	MOLD NO.	
UNIT: mm [inch]				APPROVED BY:	DATE :
SCALE:1:1	SIZE: A4	邱敏	2014-02-23	SHEET NO.	1 OF 1