









RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

性能:

额定电流: 3.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP E130I黑色

接触点(材质): 磷铜C5210, 触点镀金3U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 3.0H 4P正压电池座 有柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. MOLD NO.	HYCW-BA4P2530D-50
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2604091615
			SHEET NO.	1 OF 1