










PART NO.	DIM A	DIM B
HYCW-BA2P127225	2.54	
HYCW-BA3P127225	3.81	1.27
HYCW-BA4P127225	5.08	2.54
HYCW-BA5P127225	6.35	3.81
HYCW-BA6P127225	7.62	5.08

RECOMMENDED PCB LAYOUT

TOP VIEW (.XX±0.05)

性能:

额定电流: 1.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP E130I

接触点(材质): 铜合金, 触点镀金3u"



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X' ±2° X.X' ±0.5°

UNIT: mm [inch]

SCALE:1:1

SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

1.27PH 2.25H 正压电池座

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

SEE TABLE

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2604081028

SHEET NO.

1 OF 1