









RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)



性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

使用寿命: 5000次以上

塑件(材质): LCP BLACK

接触点(材质): 黄铜C2680,

接触面镀金3U, 焊脚镀金1U



深圳市华宇创精密电子有限公司


TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X' ±2° X.X' ±0.5°



UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

2.5PH 3.4H 4P 母座有柱

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW-BF4P2534D-50

MOLD NO.

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2604101041

SHEET NO.

1 OF 1