








RECOMMENDED PCB LAYOUT
TOL:(± 0.05)



RECOMMEND WORKING RANGE.

剖面 A-A

性能:

额定电流: 1.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30m Ω 以内

绝缘电阻: 500M Ω

工作温度: -40 $^{\circ}$ C~+85 $^{\circ}$ C

塑件(材质): LCP 黑色

接触点(材质): 铜合金, 触点镀金3U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X." ± 2 " X.X" ± 0.5 "	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 1.6PH 1.2H 6P 双排电池座
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-BAS6P1612T
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2603251613
			SHEET NO. 1 OF 1