









RECOMMENDED PCB LAYOUT
TOP VIEW(.XX±0.05)

Pin数	PART NO.	DIM A	DIM B
2Pin	HYCW-BA2P2023	4.0	2.0
3Pin	HYCW-BA3P2023	6.0	4.0
4Pin	HYCW-BA4P2023	8.0	6.0
5Pin	HYCW-BA5P2023	10.0	8.0
6Pin	HYCW-BA6P2023	12.0	10.0
7Pin	HYCW-BA7P2023	14.0	12.0
8Pin	HYCW-BA8P2023	16.0	14.0

性能:

额定电流: 3.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 触点镀金3U",

使用寿命: 5000次以上



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.0PH 2.3H 正压电池座	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2604081443
			SHEET NO.	1 OF 1