









RECOMMENDED PCB LAYOUT

TOP VIEW (. XX±0.05)

规格	DIM A	DIM B
HYCW-BF2P20127D-20	4.0	2.0
HYCW-BF3P20127D-40	6.0	4.0
HYCW-BF4P20127D-60	8.0	6.0
HYCW-BF5P20127D-80	10.0	8.0
HYCW-BF6P20127D-100	12.0	10.0
HYCW-BF7P20127D-120	14.0	12.0
HYCW-BF8P20127D-140	16.0	14.0

性能:

额定电流: 5.0A

额定电压: 30V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

使用寿命: 10000次以上

塑件(材质): PA9T黑色

接触点(材质): 黄铜C2680, 镀金



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.0PH 1.27H 母座带柱	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604081424
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1