








RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

PART NO.	DIM A	DIM B
HYCW-BB2P3068T	8.0	3.0
HYCW-BB3P3068T	11.0	6.0
HYCW-BB4P3068T	14.0	9.0
HYCW-BB5P3068T	17.0	12.0
HYCW-BB6P3068T	20.0	15.0



性能:

额定电流: 3.0A

额定电压: 24V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP, 耐高温260℃

接触点(材质): 铜合金, 触点镀金3U



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X." ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 3.0PH 6.8H 侧压电池座 立贴	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2604131548
UNIT: mm [inch] SCALE:1:1 SIZE: A4			SHEET NO.	1 OF 1