









RECOMMENDED PCB LAYOUT  
TOL:(±0.05)

|                  |       |       |       |
|------------------|-------|-------|-------|
| HYCW-BC6P2020DWT | 13.90 | 10.00 | 8.00  |
| HYCW-BC5P2020DWT | 11.90 | 8.00  | 6.00  |
| HYCW-BC4P2020DWT | 9.90  | 6.00  | 4.00  |
| HYCW-BC3P2020DWT | 7.90  | 4.00  | 2.00  |
| HYCW-BC2P2020DWT | 5.90  | 2.00  | 4.00  |
| BE FILLED        | DIM A | DIM B | DIM C |

性能:

额定电流: 5.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩMAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP 黑色

耐高温: 260度

接触点(材质): 黄铜, 接触面镀金1U"



深圳市华宇创精密电子有限公司

|                                                                            |                    |                      |                                   |                |
|----------------------------------------------------------------------------|--------------------|----------------------|-----------------------------------|----------------|
| TOLERANCE:<br>X.X ±0.30<br>X.XX ±0.25<br>X.XXX ±0.15<br>X.' ±2' X.X' ±0.5' | DRAWN BY :<br>陈一鸣  | DATE :<br>2014-02-23 | PART NAME:<br>2.0PH 刀式电池座 公座卧贴 带柱 |                |
|                                                                            | CHECKED BY:<br>马跃  | DATE :<br>2014-02-23 | PART NO.                          | SEE TABLE      |
| UNIT: mm [inch]<br>SCALE:1:1 SIZE: A4                                      | APPROVED BY:<br>邱敏 | DATE :<br>2014-02-23 | MOLD NO.                          |                |
|                                                                            |                    |                      | DRAW NO:                          | HYC-2604081643 |
|                                                                            |                    |                      | SHEET NO.                         | 1 OF 1         |