



RECOMMENDED PCB LAYOUT
TOP VIEW (XX±0.05)

PART NO.	DIM A	DIM B
HYCW-BA6P3024-C	2.4	4.30±0.25
HYCW-BA6P3035-C	3.5	5.40±0.25

性能:

额定电流: 3.0A

额定电压: 24V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP, 耐高温260℃

接触点(材质): 铜合金, 触点镀金3U



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 3.0PH 6P 正压电池座 插件脚
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO. DRAW NO: HYC-2604131155
UNIT: mm [inch] SCALE:1:1 SIZE: A4			SHEET NO. 1 OF 1