









RECOMMENDED PCB LAYOUT

TOP VIEW (.XX±0.05)

PART NO.	DIM A	DIM B
HYCW-BA2P1713-G	3.4	1.7
HYCW-BA3P1713-G	5.1	3.4
HYCW-BA4P1713-G	6.8	5.1
HYCW-BA5P1713-G	8.5	6.8
HYCW-BA6P1713-G	10.2	8.5
HYCW-BA7P1713-G	11.9	10.2

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP(黑色) UL94-V0

接触点(材质): 高导铜, 触点镀金3U",
焊脚镀雾锡70U以上, 镍30-80U"

环保要求: 符合ROHS限值。



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5" UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 1.7PH 1.3H 正压电池座 无柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2603271634
			SHEET NO.	1 OF 1