




Pin数	PART NO.	DIM A	DIM B
2P	HYCW-BP2P4040T-C	7.7	5.11
3P	HYCW-BP3P4040T-C	11.7	9.11
4P	HYCW-BP4P4040T-C	15.7	13.11
5P	HYCW-BP5P4040T-C	19.7	17.11
6P	HYCW-BP6P4040T-C	23.7	21.11

性能:

额定电流: 3A

额定电压: 30V

耐电压: 500V


接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ


工作温度: -55℃~+125℃

塑件(材质): PA9T

接触点(材质): 磷铜, 触点镀金5U



RECOMMENDED PCB LAYOUT
TOL:(±0.05)



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 4.0PH 4.0H 弹片电池座 公座 插件	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604141038
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1