










RECOMMENDED PCB LAYOUT
TOL:(±0.05)



性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP黑色

接触点(材质): 铜合金, 触点镀金3U

使用寿命: 3000次以上



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.* ±0.5*	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.0PH 2.6H 4P 正压电池座 有柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW-BA4P2026D	MOLD NO.
 UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2604081454	SHEET NO. 1 OF 1