






规格	DIM A	DIM B
HYCW-BF2P2516	5.0	
HYCW-BF3P2516D-25	7.5	2.5
HYCW-BF4P2516D-50	10.0	5.0
HYCW-BF5P2516D-75	12.5	7.5
HYCW-BF6P2516D-100	15	10.0

性能:

额定电流: 3.0A

额定电压: 60V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

使用寿命: 10000次以上

塑件(材质): PA9T

接触点(材质): 黄铜C2680, 镀金

RECOMMENDED PCB LAYOUT

TOP VIEW (.XX±0.05)



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 1.6H 电池母座 带柱	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-20200604163
			SHEET NO.	1 OF 1