









RECOMMENDED PCB LAYOUT
TOL:(± 0.05)



规格型号	DIM A	DIM B
HYCW-BB4P3072-C	7.2	5.5
HYCW-BB4P3065-C	6.5	4.8
HYCW-BB4P3050-C	5.0	3.3
HYCW-BB4P3046-C	4.6	2.9



性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -40℃ ~ +85℃

塑件 (材质): LCP 黑色

接触点 (材质): 铜合金



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' ± 2 X.X' ± 0.5	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 3.0PH 4P 侧压电池座 插件脚	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2604131516
			SHEET NO.	1 OF 1