










PART NO.	DIM A	DIM B
HYCW-BA2P12717L	2.54	
HYCW-BA3P12717L	3.81	1.27
HYCW-BA4P12717L	5.08	2.54
HYCW-BA5P12717L	6.35	3.81
HYCW-BA6P12717L	7.62	5.08
HYCW-BA7P12717L	8.89	6.35
HYCW-BA8P12717L	10.16	7.62

性能:

额定电流: 1.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ MAX

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP E130I

接触点(材质): 铜合金, 触点镀金3u"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 1.27PH 1.7H 正压电池座	
		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
  UNIT: mm [inch]		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604080953
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1

RECOMMENDED PCB LAYOUT

TOP VIEW(.XX±0.05)