









剖面 A-A

RECOMMENDED PCB LAYOUT
TOP VIEW (.XX±0.05)

性能:

额定电流: 1.0A

额定电压: 12V

耐压: 500V

接触电阻: 30mΩ 以内

绝缘电阻: 500MΩ

工作温度: -40℃~+85℃

塑件(材质): LCP 黑色

接触点(材质): 铜合金, 触点镀金3U"



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 1.6PH 1.2H 4P 双排电池座	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HWCW-BAS4P1612T	MOLD NO.
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2603251605	SHEET NO. 1 OF 1