






RECOMMENDED PCB LAYOUT
TOP VIEW (.XX $\pm$ 0.05)



PART NO.	DIM A	DIM B
HYCW-BA8P2524F-C	2.4	4.30 $\pm$ 0.2
HYCW-BA8P2530F-C	3.0	4.90 $\pm$ 0.2
HYCW-BA8P2535F-C	3.5	5.40 $\pm$ 0.2

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30m Ω 以内

绝缘电阻: 500M Ω

工作温度: -40 $^{\circ}$ C~+85 $^{\circ}$ C

使用寿命: 5000次以上

塑件(材质): LCP(黑色) UL94-V0

接触点(材质): 锡磷青铜, 触点镀金3U",
焊脚镀金1U"

固定片(材质): 黄铜C2680, 镀全雾锡70U"以上

环保要求: 符合ROHS限值。



深圳市华宇创精密电子有限公司

TOLERANCE: X.X $\pm$ 0.30 X.XX $\pm$ 0.25 X.XXX $\pm$ 0.15 X.' $\pm$ 2' X.X' $\pm$ 0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 8P 正压电池座 插件脚	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2604291653
			SHEET NO.	1 OF 1