






RECOMMENDED PCB LAYOUT
TOL:(± 0.05)



性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30m Ω

绝缘电阻: 500M Ω

工作温度: -40 $^{\circ}$ C~+85 $^{\circ}$ C

塑件(材质): LCP

接触点(材质): 磷铜, 镀金

规格	DIM A	DIM B	DIM C
HYCW-BB3P3072D-30	7.2	5.5	6.5
HYCW-BB3P3068D-30	6.8	5.1	6.1
HYCW-BB3P3060D-30	6.0	4.3	5.3
HYCW-BB3P3054D-30	5.4	3.7	4.7
HYCW-BB3P3050D-30	5.0	3.3	4.3
HYCW-BB3P3046D-30	4.6	2.9	3.9




深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30
X.XX ± 0.25
X.XXX ± 0.15

X' $\pm 2^{\circ}$ X.X' $\pm 0.5^{\circ}$



UNIT: mm [inch]

SCALE: 1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

3.0PH 3P 侧压电池座 3.0柱

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

SEE TABLE

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-202006051630

SHEET NO.

1 OF 1