






Pin数	PART NO.	DIM A	DIM B
2P	HYCW-BP2P4040DT-51	7.7	5.11
3P	HYCW-BA3P4040DT-91	11.7	9.11
4P	HYCW-BA4P4040DT-131	15.7	13.11
5P	HYCW-BA5P4040DT-171	19.7	17.11
6P	HYCW-BA6P4040DT-211	23.7	21.11

性能:

额定电流: 3A

额定电压: 30V

耐电压: 500V




接触电阻: 30mΩ

绝缘电阻: 500MΩ

工作温度: -55℃~+125℃

塑件(材质): PA9T

接触点(材质): 磷铜, 镀金5U



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30

X.XX ±0.25

X.XXX ±0.15

X.' ±2' X.X' ±0.5'

UNIT: mm [inch]

SCALE:1:1

SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

CHECKED BY :

马跃

DATE :

2014-02-23

APPROVED BY :

邱敏

DATE :

2014-02-23

PART NAME:

4.0PH 4.0H 弹片电池座 公座有柱

PART NO.

SEE TABLE

MOLD NO.

DRAW NO: HYC-2604141042

SHEET NO.

1 OF 1