


RECOMMENDED PCB LAYOUT
TOL:(<±0.05)

HYCW-BB6P2563D-C100	12.50	16.30	10.00	15.40
HYCW-BB5P2563D-C75	10.00	13.80	7.50	12.90
HYCW-BB4P2563D-C50	7.50	11.30	5.00	10.40
规格型号	A	B	C	D

性能:

额定电流: 2.0A

额定电压: 12V

耐电压: 500V

接触电阻: 30mΩ

绝缘电阻: 500MΩ


工作温度: -40℃~+85℃

塑件(材质): LCP

接触点(材质): 磷铜, 镀金



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 2.5PH 6.3H 侧压电池座 有柱	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	SEE TABLE
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604101623
				SHEET NO.	1 OF 1
SCALE:1:1	SIZE: A4				