





Ass'y High(H)	Plastic High	
	Male (H1)	Female (H2)
8.00	6.90	6.00
10.00	8.90	6.00



SPECIFICATIONS  
 PERFORMANCE  
 Current Rating (信号端子): 0.5A  
 Current Rating (电源端子): 5A  
 Contact Resistance: 80mΩ Max  
 Insulation Resistance: 500MΩ Min  
 Withstand Volt: 200V AC/minute  
 Oprating Temperature: -40°C to +105°C

Material  
 Contact: Phosphor Bronze, 3u" MIN Gold Plated In Contact Area,  
 Gold Flash Plated In Solder Area,  
 50u"~240u" Nickel Underplated Over all.  
 Ground: Brass, 80u" Min Matte Tin Plated Over  
 50u" Min Nickel Underplated Over all.  
 Housing: LCP Black, UL94V0  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)

**Ordering Information**

HC-PBB23L - NDS - 0.5V - \*\* - 01

No of Pins	Nature DS=Female	PITCH 0.5V=0.5mm	Contact Plating
30-120Pin			G2.3u" Gold
30-100Pin			S0.1u" Gold/Tin
50-50Pin			S1.5u" Gold/Tin
			S2.5u" Gold/Tin
			S3.10u" Gold/Tin
			S4.15u" Gold/Tin
			S5.30u" Gold/Tin

		GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
		DIM TOL	审核 CHECK	产品名称 TITLE	BTB 0.5 高频大电流 浮动式 H6.0 贴片母座 带柱	版本 REV.	A
		X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	HC-PBB23L-40DS-0.5V-XX-01	单位 UNITS	mm
1	初版发行	X.XX ±0.20	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	X.XXX ±0.10					
	日期 MODIFY DATE	Angle ±3.0°					