










REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



适用扁平线(Applicable Flat Cable)



适用线路板(PCB LAYOUT)

Part No	Pin	A	B	C	D
JXT-AFC05-AX4P-H20	4	1.50	2.56	7.60	5.20
JXT-AFC05-AX5P-H20	5	2.00	3.06	8.10	
JXT-AFC05-AX6P-H20	6	2.50	3.56	8.60	
JXT-AFC05-AX7P-H20	7	3.00	4.06	9.10	
JXT-AFC05-AX8P-H20	8	3.50	4.56	9.60	
JXT-AFC05-AX9P-H20	9	4.00	5.06	10.10	
JXT-AFC05-AX10P-H20	10	4.50	5.56	10.60	
JXT-AFC05-AX11P-H20	11	5.00	6.06	11.10	
JXT-AFC05-AX12P-H20	12	5.50	6.56	11.60	5.75
.....					
JXT-AFC05-AX34P-H20	34	16.50	17.56	22.60	
JXT-AFC05-AX35P-H20	35	17.00	18.06	23.10	
JXT-AFC05-AX36P-H20	36	17.50	18.56	23.60	
.....		...			
JXT-AFC05-AX60P-H20	60	(60-1)*0.5	(60+1)*0.5+0.06	(60+11)*0.5+0.1	

序号	品名	材质
1	0.5拉拔胶芯(H2.0)	LCP UL94V-0 本色
2	0.5拉拔下端子(H2.0)	铜合金/表面镀锡
3	0.5拉拔胶式后盖(H2.0)	LCP UL94V-0 黑色
4	0.5拉拔焊片(H2.0)	铜合金/表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC/DC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 500M\Omega$ 。

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X*±5°	PART NO.	TITLE: 0.5 Pitch H2.0 ZIF		
.XX±0.20	.XX*±2°	JXT-AFC05-AXNP-H20	R/A Type 3 Unper CONN.		
.XXX±0.05	.XXX*±1°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	---	APPD: Ava		N:A	1/1
FINISH	---				