





RoHS compliant



PC Board Layout

NOTES

MATERIAL

1. HOUSING MATERIAL : PBT UL94V-0.
2. CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3. PLATING : GOLD PLATING OVER NICKEL.
: FU", 3U", 6U", 15U", 30", 50".

ELECTRICAL


1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 500V DC .
5. DIELECTRIC RESISTANCE : 1000V AC RMS 50Hz. 1MIN.

MECHANICAL

1. DURRABILITY : 750 CYCLES MIN.
2. PCB RETENTIONPRE-SOLDER : 1 LB MIN.

ENVIRONMENTAL:

1. STORAGE : $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. OPERATION : $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



P/N:RJ5JA-8811-001111R

5JA RJ45 SERIES PCB JACK

POSITIONS (金針位置):

8-8POSITIONS (8P)

CONTACTS (金針根數):

8-8CONTACTS (8C)

PORTS (窗口):

14-14

SHIELD (屏蔽壳):

0-Without SHIELD (全塑)

BACK PEG (定位柱):

0-Without BACK PEG (无定位脚)

LED STYLE (LED 顏色类型):

1-LED LEFT:YELLOW, LED RIGHT:GREEN (左黄右绿)

2-LED LEFT:GREEN, LED RIGHT:YELLOW (左绿右黄)

PIN STYLE (PIN規格):

R-ROUND PIN (圓針)

F-FLAT PIN (扁針)

COLOR (顏色):

1-BLACK (黑色)

4-YELLOW (黃色)

PLASTIC (塑料):

1-PBT

GOLD PLATING (鍍金厚度):

1-10"; 2-1.50"; 3-30"; 4-60";

5-150"; 6-300"; 7-500";

					GENERAL TOLERANCE		DRAWN		Gene Li		2016/04/10		 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD				
					.X	±0.35	X.°	± 2°	CHECKE		JL						
A0		NEW DESIGN		2016/04/10		.XX	±0.25	X.°	± 1°	APPROVE				PART NO.		RJ5JA-8811-001111R	
						.XXX	±0.15	.XX°	± 0.5°					TITLE:		RJ45 8P8C 1X1 BLACK, LED L/YELLOW, R/GRENN	
REV	ECN NO	DESCRIPTION		DATE	SIGNATURE	PROJECT			UNIT: mm		SCALE: 1:1	SHEET: 1/1	REV: A0				
																	