







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
JXT-PZ2.54-1X1P-A1	1	0.00	2.54
JXT-PZ2.54-1X2P-A1	2	2.54	5.08
JXT-PZ2.54-1X3P-A1	3	5.08	7.62
JXT-PZ2.54-1X4P-A1	4	7.62	10.16
JXT-PZ2.54-1X5P-A1	5	10.16	12.70
JXT-PZ2.54-1X6P-A1	6	12.70	15.24
JXT-PZ2.54-1X7P-A1	7	15.24	17.78
JXT-PZ2.54-1X8P-A1	8	17.78	20.32
JXT-PZ2.54-1X9P-A1	9	20.32	22.86
.....			
JXT-PZ2.54-1X40P-A1	40	(40-1)X2.54	(40)X2.54

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. JXT-PZ2.54-1XNP-A1		TITLE: 2.54PH H2.5 1xnPin 180# PC3.0 PA6.0 PB2.5 L11.5 6T	
.XX ±0.20	X.X° ±1°				
.XXX ±0.10	X.XX° ±0.5°				
UNITS	mm	DESIGN: Ethan		MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1