


XH连接器承认图面



使用温度范围 (Ambient temperature Range):-25°~+85°

适用线规 (Applicable Wires):AWG 30#~22#

额定电压 (Voltage rating):250V AC,DC

额定电流 (Current rating):3A

接触电阻 (Contact Resistance):<0.01Ω


绝缘电阻 (Insulation Resistance):>1000MΩ

耐压 (Withstand Voltange):1000VAC/min

材料 (Material)

1.基座: PA66 94V-0(2)

孔位	A-mm	B-mm	C-mm
XH-2Y	5.7	2.5	7.3
XH-3Y	8.2	5.0	9.8
XH-4Y	10.7	7.5	12.3
XH-5Y	13.2	10.0	14.8
XH-6Y	15.7	12.5	17.3
XH-7Y	18.2	15.0	19.8
XH-8Y	20.7	17.5	22.3
XH-9Y	23.2	20.0	24.8
XH-10Y	25.7	22.5	27.3
XH-11Y	28.2	25.0	29.8
XH-12Y	30.7	27.5	32.3
XH-13Y	33.2	30.0	34.8
XH-14Y	35.7	32.5	37.3
XH-15Y	38.2	35.0	39.8
XH-16Y	40.7	37.5	42.3

2		Wafer 针		Brass Tin 黄铜镀锡		N													
1		Housing 基座		PA66 94V-0(2)		1													
序号		图号		名称		材料		数量		附注									
未注公差				 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD															
X.°±3° X.X°±5°																			
>0-3		>3-18		>18-50		>50-120						Design Units		SIZE					
±0.12		±0.15		±0.3		±0.5		MMOnly		——		METRIC		A4					
制作		审核		批准		材料		图号				Part No.		LXW-XH-nY					
						见图解		品名				XH-NY							