





技术参数:

PIN数: 2~12
适用线规: AWG22#~18#

适用基板厚度: 1.6mm

温度范围: -25℃~85℃

额定电压: 250V AC/DC

额定电流: 7.5A

接触电阻: ≤0.015 Ω

绝缘电阻: ≥1000N Ω

耐压: 1500V AC/minute

材料: (Nylon)66UL94V-2(0)

Part No	Pin	A	B
JXT-VH3.96-2PJK-AD	2	3.96	8.07
JXT-VH3.96-3PJK-AD	3	7.92	12.03
JXT-VH3.96-4PJK-AD	4	11.88	15.99
JXT-VH3.96-5PJK-AD	5	15.84	19.95
JXT-VH3.96-6PJK-AD	6	19.8	23.91
JXT-VH3.96-7PJK-AD	7	23.76	27.87
JXT-VH3.96-8PJK-AD	8	27.72	31.83
JXT-VH3.96-9PJK-AD	9	31.68	35.79
JXT-VH3.96-10PJK-AD	10	35.64	39.75
JXT-VH3.96-11PJK-AD	11	39.6	43.71
JXT-VH3.96-12PJK-AD	12	43.58	47.67

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.35	X.° ±5°	PART NO. JXT-VH3.96-NPJK-AD	TITLE: VH3.96MM HOUSING		
.XX ±0.25	X.X° ±3°		MANUFACTURE DWG		
.XXX ±0.15	X.XX° ±1°				
UNITS	mm	DESIGN:	Ethan	 SCALE N:A	
MATERILA	— — —	CHED:	Olvia		
FINISH	— — —	APPD:	Ava		
				SHEET	1/1