







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS
Current Rating: 1.0 Amps
Withstanding Voltage:AC 500V
Insulation Resistance:1000MΩ Min
Contact Resistance:20mΩ Max
Operation Temperature:-40°to+105°
Insrlator Material:Polyester(UL94V-0)
Contact Material:Phosphor bronze
Standard:PA6T
Contact Plating:Gold Flash
Max.Processing Temp:
240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
JXT-PM1.27-1X1P-A1	1	0.00	1.27
JXT-PM1.27-1X2P-A1	2	1.27	2.54
JXT-PM1.27-1X3P-A1	3	2.54	3.81
JXT-PM1.27-1X4P-A1	4	3.81	5.08
JXT-PM1.27-1X5P-A1	5	5.08	6.35
JXT-PM1.27-1X6P-A1	6	6.35	7.62
JXT-PM1.27-1X7P-A1	7	7.62	8.89
JXT-PM1.27-1X8P-A1	8	8.89	10.16
JXT-PM1.27-1X9P-A1	9	10.16	11.43
.....			
JXT-PM1.27-1X50P-A1	50	(50-1)x1.27	(50)x1.27



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.° ±5°	PART NO. JXT-PM1.27-1XNP-A1	TITLE:1.27FH H4.3 1xNPin 180度 W2.1 U型 PC2.4 6T	
.XX ±0.20	X.X° ±1°		MANUFACTURE DWG	
.XXX ±0.10	X.XX° ±0.5°			
UNITS	mm	DESIGN:	Ethan	
MATERILA	— — —	CHED:	Olvia	
FINISH	— — —	APPD:	Ava	
				SCALE N:A
				SHEET 1/1