





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
JXT-PM2.54-2X1P-A9	2*1	0.00	2.54
JXT-PM2.54-2X2P-A9	2*2	2.54	5.08
JXT-PM2.54-2X3P-A9	2*3	5.08	7.62
JXT-PM2.54-2X4P-A9	2*4	7.62	10.16
JXT-PM2.54-2X5P-A9	2*5	10.16	12.70
JXT-PM2.54-2X6P-A9	2*6	12.70	15.24
JXT-PM2.54-2X7P-A9	2*7	15.24	17.78
JXT-PM2.54-2X8P-A9	2*8	17.78	20.32
JXT-PM2.54-2X9P-A9	2*9	20.32	22.86
.....			
JXT-PM2.54-2X40P-A9	2*40	(40-1)X2.54	(40)X2.54

TOLERANCE			 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO.	TITLE: 2.54FH H8.5 2xnPin 180度 Y型 PC3.2 6T		
.XX ±0.20	X.* ±1°	JXT-PM2.54-2XNP-A9			
.XXX ±0.10	X.XX ±0.5°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm				
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1