






SPECIFICATIONS
Current Rating: 1.0 Amps
Withstanding Voltage: AC 500V
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Operation Temperature: -40° to +105°
Insulator Material: Polyester (UL94V-0)
Contact Material: Phosphor bronze
Standard: PA6T
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
JXT-PM1.27-2X1P-A2	2*1	0.00	1.27
JXT-PM1.27-2X2P-A2	2*2	1.27	2.54
JXT-PM1.27-2X3P-A2	2*3	2.54	3.81
JXT-PM1.27-2X4P-A2	2*4	3.81	5.08
JXT-PM1.27-2X5P-A2	2*5	5.08	6.35
JXT-PM1.27-2X6P-A2	2*6	6.35	7.62
JXT-PM1.27-2X7P-A2	2*7	7.62	8.89
JXT-PM1.27-2X8P-A2	2*8	8.89	10.16
JXT-PM1.27-2X9P-A2	2*9	10.16	11.43
.....			
JXT-PM1.27-2X50P-A2	2*50	(50-1)x1.27	(50)x1.27

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X	±0.30	X.*	±5°	PART NO.	TITLE: 1.27FH H4.3 2xNPin
.XX	±0.20	X.X*	±1°	JXT-PM1.27-2XNP-A2	SMT U ₁ PC4.8 PB4.6 6T
.XXX	±0.10	X.XX*	±0.5°	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm				
MATERILA	---			CHED: Olvia	
FINISH	---			APPD: Ava	
					SCALE SHEET N:A 1/1