




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
JXT-PM2.54-1X1P-A9	1	0.00	2.54
JXT-PM2.54-1X2P-A9	2	2.54	5.08
JXT-PM2.54-1X3P-A9	3	5.08	7.62
JXT-PM2.54-1X4P-A9	4	7.62	10.16
JXT-PM2.54-1X5P-A9	5	10.16	12.70
JXT-PM2.54-1X6P-A9	6	12.70	15.24
JXT-PM2.54-1X7P-A9	7	15.24	17.78
JXT-PM2.54-1X8P-A9	8	17.78	20.32
JXT-PM2.54-1X9P-A9	9	20.32	22.86
.....			
JXT-PM2.54-1X40P-A9	40	(40-1)X2.54	(40)X2.54



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO.	TITLE: 2.54FH H8.5 1xnPin	
.XX ±0.20	X.X* ±1°	JXT-PM2.54-1XNP-A9	180度 Y型 PC3.2 6T	
.XXX ±0.10	X.XX*±0.5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---			N:A
				1/1