








技术要求Specification:

1. 材质Material: PA66 UL94V-0:
2. 额定电流 Current rating:3.0A AC,DC
3. 额定电压 Voltage rating:250V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:1000V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
JXT-HA2.54-2PJK-P11	2	2.50	5.80
JXT-HA2.54-3PJK-P11	3	5.00	8.30
JXT-HA2.54-4PJK-P11	4	7.50	10.80
JXT-HA2.54-5PJK-P11	5	10.00	13.30
JXT-HA2.54-6PJK-P11	6	12.50	15.80
JXT-HA2.54-7PJK-P11	7	15.00	18.30
JXT-HA2.54-8PJK-P11	8	17.50	20.80
JXT-HA2.54-9PJK-P11	9	20.00	23.30
JXT-HA2.54-10PJK-P11	10	22.50	25.80
JXT-HA2.54-11PJK-P11	11	25.00	28.30
JXT-HA2.54-12PJK-P11	12	27.50	30.80
JXT-HA2.54-13PJK-P11	13	30.00	33.30
JXT-HA2.54-14PJK-P11	14	32.50	35.80
JXT-HA2.54-15PJK-P11	15	35.00	38.30
JXT-HA2.54-16PJK-P11	16	37.50	40.80
JXT-HA2.54-17PJK-P11	17	40.00	43.30

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X	±0.30	X.*	±1°	PART NO.
.XX	±0.20			JXT-HA2.54-NPJK-P11
.XXX	±0.10			DESIGN: Ethan
UNITS	mm			CHED: Olvia
MATERILA	---			APPD: Ava
FINISH	---			
		TITLE: HA2.5MM HOUSING		MANUFACTURE DWG
		SCALE N:A		SHEET 1/1