








| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |
|      |         |             |      |        |


NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 3A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 1000V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

| Part No              | Pin | A     | B     | C     |
|----------------------|-----|-------|-------|-------|
| JXT-HA2.54-2PWB-P43  | 2   | 2.50  | 10.00 | 8.30  |
| JXT-HA2.54-3PWB-P43  | 3   | 5.00  | 12.50 | 10.80 |
| JXT-HA2.54-4PWB-P43  | 4   | 7.50  | 15.00 | 13.30 |
| JXT-HA2.54-5PWB-P43  | 5   | 10.00 | 17.50 | 15.80 |
| JXT-HA2.54-6PWB-P43  | 6   | 12.50 | 20.00 | 18.30 |
| JXT-HA2.54-7PWB-P43  | 7   | 15.00 | 22.50 | 20.80 |
| JXT-HA2.54-8PWB-P43  | 8   | 17.50 | 25.00 | 23.30 |
| JXT-HA2.54-9PWB-P43  | 9   | 20.00 | 27.50 | 25.80 |
| JXT-HA2.54-10PWB-P43 | 10  | 22.50 | 30.00 | 28.30 |
| JXT-HA2.54-11PWB-P43 | 11  | 25.00 | 32.50 | 30.80 |
| JXT-HA2.54-12PWB-P43 | 12  | 27.50 | 35.00 | 33.30 |
| JXT-HA2.54-13PWB-P43 | 13  | 30.00 | 37.50 | 35.80 |
| JXT-HA2.54-14PWB-P43 | 14  | 32.50 | 40.00 | 38.30 |
| JXT-HA2.54-15PWB-P43 | 15  | 35.00 | 42.50 | 40.80 |
| JXT-HA2.54-16PWB-P43 | 16  | 37.50 | 45.00 | 43.30 |

|            |           |                                                                                                                                                                             |                                                                                       |       |       |
|------------|-----------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------|-------|
| TOLERANCE  |           | <div> 深圳聚兴泰电子科技有限公司</div> <div>Shenzhen Juxingtai Electronic Technology Co., Ltd</div> |                                                                                       |       |       |
| X.X ±0.30  | X.* ±5°   | PART NO.                                                                                                                                                                    | TITLE:                                                                                |       |       |
| .XX ±0.20  | X.X* ±3°  | JXT-HA2.54-NPWB-P43                                                                                                                                                         | WAFER XHB2.54 卧贴带扣                                                                    |       |       |
| .XXX ±0.10 | X.XX* ±1° | DESIGN: Ethan                                                                                                                                                               | MANUFACTURE DWG                                                                       |       |       |
| UNITS      | mm        | CHED: Olvia                                                                                                                                                                 |  | SCALE | SHEET |
| MATERILA   | — — —     | APPD: Ava                                                                                                                                                                   |                                                                                       | N:A   | 1/1   |