


2PIN结构



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.5
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 3A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 1000V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C
JXT-XH2.54-2PLB-P43	2	2.50	10.00	7.50
JXT-XH2.54-3PLB-P43	3	5.00	12.50	10.00
JXT-XH2.54-4PLB-P43	4	7.50	15.00	12.50
JXT-XH2.54-5PLB-P43	5	10.00	17.50	15.00
JXT-XH2.54-6PLB-P43	6	12.50	20.00	17.50
JXT-XH2.54-7PLB-P43	7	15.00	22.50	20.00
JXT-XH2.54-8PLB-P43	8	17.50	25.00	22.50
JXT-XH2.54-9PLB-P43	9	20.00	27.50	25.00
JXT-XH2.54-10PLB-P43	10	22.50	30.00	27.50
JXT-XH2.54-11PLB-P43	11	25.00	32.50	30.00
JXT-XH2.54-12PLB-P43	12	27.50	35.00	32.50
JXT-XH2.54-13PLB-P43	13	30.00	37.50	35.00
JXT-XH2.54-14PLB-P43	14	32.50	40.00	37.50
JXT-XH2.54-15PLB-P43	15	35.00	42.50	40.00
JXT-XH2.54-16PLB-P43	16	37.50	45.00	42.50

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO.	TITLE:	
.XX ±0.20	X.X* ±3°	JXT-XH2.54-NPLB-P43	WAFER 2.54 立贴	
.XXX ±0.10	X.XX* ±1°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---		N:A	1/1

