





NO.	ECN NO.	DESCRIPTION	DATE
-----	---------	-------------	------



Note:

1: Material (材料):

Housing: PA46+30%GF (胶芯: PA46)

PIN: Brass C3604 (针: 黄铜 C3604)

2: Plating (电镀):

Pin: 3u' Au over 50~80' u Ni (针: 镀金3u', 镍底50~80u'。)

3: Electrical (电气特性):

Rated Current & Voltage: DC 12V; 3A (额定电压&电流: 直流12V, 3A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

Insulation Resistance: 1,000MΩ minimum. (绝缘电阻: 1,000MΩ以上)

Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)

4: WorkTemperature (工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: - 20℃~ + 70℃

深圳市鑫探技术有限公司										THE UNMARKED TOLERANCE ARE AS BELOW :									
HTTP://WWW.XYZPOGOPIN.COM										LENGTH									
TEL:0755-28773277 FAX:0755-28891353										ANGLE									
										DESIGNED BY:									
SCALE: N/A										UNIT									
SHEET: 1 of 1										PROJECTION									
DATE: 2026.04.21										VER.									
D.0										X.XX ±0.05mm									
X.XX ±0.10mm										X.XX ±0.50°									
X.XX ±0.20mm										X.XX ±1.00mm									
X.XX ±2.00°										APPROVED BY:									
DWG. NO.										TITLE:									
YZ1805150848-08025-01										Pogo pin连接器									