







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Insulator Material: Polyester(UL 94V-0)
Contact plating: Gold Flash
Standard: PA6T
Max.Processing Temp: 240°C for30-60seconds
(260°Cfor10seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
JXT-IDC2.54-2X3P-A1	2*3	5.08	7.62
JXT-IDC2.54-2X4P-A1	2*4	7.62	10.16
JXT-IDC2.54-2X5P-A1	2*5	10.16	12.70
JXT-IDC2.54-2X6P-A1	2*6	12.70	15.24
JXT-IDC2.54-2X7P-A1	2*7	15.24	17.78
JXT-IDC2.54-2X8P-A1	2*8	17.78	20.32
JXT-IDC2.54-2X9P-A1	2*9	20.32	22.86
JXT-IDC2.54-2X10P-A1	2*10	22.86	25.40
JXT-IDC2.54-2X12P-A1	2*12	27.94	30.48
JXT-IDC2.54-2X13P-A1	2*13	30.48	33.02
JXT-IDC2.54-2X14P-A1	2*14	33.02	35.56
JXT-IDC2.54-2X15P-A1	2*15	35.56	38.10
JXT-IDC2.54-2X16P-A1	2*16	38.10	40.64
JXT-IDC2.54-2X17P-A1	2*17	40.64	43.18
JXT-IDC2.54-2X18P-A1	2*18	43.18	45.72
JXT-IDC2.54-2X20P-A1	2*20	48.26	50.80
JXT-IDC2.54-2X22P-A1	2*22	53.34	55.88
JXT-IDC2.54-2X25P-A1	2*25	60.96	63.50
JXT-IDC2.54-2X30P-A1	2*30	73.66	76.20
JXT-IDC2.54-2X32P-A1	2*32	78.74	81.28

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.±0.30	X.*±5°	PART NO. JXT-IDC2.54-2XNP-A1	TITLE: 2.54DC3-NPIn H8.9 180度 PC3.2 L11.5 6T	
X.X±0.20	X.X*±2°			
X.XX±0.10	X.XX*±1°			
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	---	CHED: Olvia		
FINISH	---	APPD: Ava		SCALE N:A
				SHEET 1/1