






Technical Index:


1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. Rated voltage: 200V
3. Rated current: 2.0A.
4. Contact resistance: $\leq 25\text{m}\Omega$.
5. Withstanding voltage: 500V
6. Insulation resistance: $\geq 1000\text{M}\Omega$.



SECTION A-A

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
JXT-PH2.0-2PZZ-H1	2	2.00	6.00
JXT-PH2.0-3PZZ-H1	3	4.00	8.00
JXT-PH2.0-4PZZ-H1	4	6.00	10.00
JXT-PH2.0-5PZZ-H1	5	8.00	12.00
JXT-PH2.0-6PZZ-H1	6	10.00	14.00
JXT-PH2.0-7PZZ-H1	7	12.00	16.00
JXT-PH2.0-8PZZ-H1	8	14.00	18.00
JXT-PH2.0-9PZZ-H1	9	16.00	20.00
JXT-PH2.0-10PZZ-H1	10	18.00	22.00
JXT-PH2.0-11PZZ-H1	11	20.00	24.00
JXT-PH2.0-12PZZ-H1	12	22.00	26.00
JXT-PH2.0-13PZZ-H1	13	24.00	28.00
JXT-PH2.0-14PZZ-H1	14	26.00	30.00
JXT-PH2.0-15PZZ-H1	15	28.00	32.00
JXT-PH2.0-16PZZ-H1	16	30.00	34.00
JXT-PH2.0-17PZZ-H1	17	32.00	36.00
JXT-PH2.0-18PZZ-H1	18	34.00	38.00
JXT-PH2.0-19PZZ-H1	19	36.00	40.00
JXT-PH2.0-20PZZ-H1	20	38.00	42.00



适用线路板(PCB LAYOUT)

序号	品名	材质
1	PH2.0 直针 胶芯	PA66 UL94V-2 Yellow
2	PH2.0 直针 端子	Copper Alloy/ Tin Plating

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X:±0.35	X.X':±3"	PART NO. JXT-PH2.0-NPZZ-H1	TITLE: Socket-type terminal Vertical plug		
X.XX:±0.25	X.XX':±2"				
X.XXX:±0.15					
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1