








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
JXT-XH2.54-2PWZ-R1	2	2.5	7.5
JXT-XH2.54-3PWZ-R1	3	5.0	10.0
JXT-XH2.54-4PWZ-R1	4	7.5	12.5
JXT-XH2.54-5PWZ-R1	5	10.0	15.0
JXT-XH2.54-6PWZ-R1	6	12.5	17.5
JXT-XH2.54-7PWZ-R1	7	15.0	20.0
JXT-XH2.54-8PWZ-R1	8	17.5	22.5
JXT-XH2.54-9PWZ-R1	9	20.0	25.0
JXT-XH2.54-10PWZ-R1	10	22.5	27.5
JXT-XH2.54-11PWZ-R1	11	25.0	30.0
JXT-XH2.54-12PWZ-R1	12	27.5	32.5
JXT-XH2.54-13PWZ-R1	13	30.0	35.0
JXT-XH2.54-14PWZ-R1	14	32.5	37.5
JXT-XH2.54-15PWZ-R1	15	35.0	40.0
JXT-XH2.54-16PWZ-R1	16	37.5	42.5




序号	品名	材质
1	XH2.5 胶芯	PA66 UL94V-2 Red
2	XH2.5 弯针 端子	Copper Alloy/ Tin Plating

Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 3.0A.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Withstanding voltage: 1000V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.

适用线路板(PCB LAYOUT)

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
X.X:±0.35	X.X':±3"	PART NO.	TITLE: Socket-type terminal Vertical plug
X.XX:±0.25	X.XX':±2"	JXT-XH2.54-NPWZ-R1	
X.XXX:±0.15		DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia	
MATERILA	---	APPD: Ava	
FINISH	---		
			 SCALE N:A SHEET 1/1