




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术要求Specification:

- 1、材质Material: PA66 UL94V-0;
- 2、额定电流 Current rating:3.0A AC,DC
- 3、额定电压 Voltage rating:250V AC,DC
- 4、温度范围 Temperature range:-25℃to+85℃
- 5、接触电阻 Contact resistance:≤20mΩ
- 6、绝缘电阻Insulation resistance:≥1000MΩ
- 7、耐压Withstand voltage:1000V AC/minute
- 8、塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

Part No	Pin	A	B	C	D
JXT-XH2.54-2PJK-P11	2	2.50	5.70	3.70	3.70
JXT-XH2.54-3PJK-P11	3	5.00	8.20	6.20	6.20
JXT-XH2.54-4PJK-P11	4	7.50	10.70	8.70	8.70
JXT-XH2.54-5PJK-P11	5	10.00	13.20	11.20	11.20
JXT-XH2.54-6PJK-P11	6	12.50	15.70	13.70	13.70
JXT-XH2.54-7PJK-P11	7	15.00	18.20	16.20	16.20
JXT-XH2.54-8PJK-P11	8	17.50	20.70	18.70	18.70
JXT-XH2.54-9PJK-P11	9	20.00	23.20	21.20	21.20
JXT-XH2.54-10PJK-P11	10	22.50	25.70	23.70	23.70
JXT-XH2.54-11PJK-P11	11	25.50	28.20	26.20	26.20
JXT-XH2.54-12PJK-P11	12	27.50	30.70	28.70	28.70
JXT-XH2.54-13PJK-P11	13	30.00	33.20	31.20	31.20
JXT-XH2.54-14PJK-P11	14	32.50	35.70	33.70	33.70
JXT-XH2.54-15PJK-P11	15	35.50	38.20	36.20	36.20
JXT-XH2.54-16PJK-P11	16	37.50	40.70	38.70	38.70

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X	±0.30	X.*	±1°	PART NO.	TITLE:
.XX	±0.20			JXT-XH2.54-NPJK-P11	XH2.5MM HOUSING
.XXX	±0.10			DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm			CHED: Olvia	 SCALE SHEET N:A 1/1
MATERILA	---			APPD: Ava	
FINISH	---				

