

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN






Specifications:

Electrical:


- Current Rating
1.5A/contact terminal
- Voltage Rating
30V DC
- Contact Resistance
30 milliohms MAX
- Dielectric Withstanding Voitage:
500 V AC AT Sea Levol
- Lnsulation Resistance:
1000MEGA ohms MIN

Mechanical:

- Cnnector Mate and Unmate ForceMate
Mate force:3.75kgf (MAX)
Unmate force:1.02kgf (MIN)
 - Terminal Retenion1.2kgf (MIN)
- Material:
- Housing:Hing Temperature Tnermaplastics,UL 94V-0 PBT/LCP White/Black
 - Contact:Copper Alloy C2680
 - Shell: Copper Alloy C2680/SPCC
- Finish:
- Contact: Piated Gold in Mating Area;Tin On Solder Talls
 - Shell: Nickel Plating



Pin Definition		
PIN	Signal Name	Describe
1	VBUS	+5V
2	D-	Neagative Data Channel
3	D+	Positive Data Channel
4	GND	Ground



PCB.WELDING DRAWING (TOLERANCE:±0.05)

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.*±5°	PART NO. JXT-USB-AMR180	TITLE: USB-AM-SMD-90°		
.XX±0.25	X.X°±1°		MANUFACTURE DWG		
.XXX±0.15		DESIGN: Ethan			
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	---	APPD: Ava		N:A	1/1