





客户图纸

NO.	ECN NO.	DESCRIPTION	DATE



RECOMMENDED PCB LAYOUT



Note:

1: Material (材料):

Housing: PA46+30%GF (胶芯: PA46)

Pin: Brass C3604 (针: 黄铜 C3604)

2: Plating (电镀):

Pin: 3u' Au over 50~80u' Ni (针: 镀金3u', 镍底50~80u'.)

3: Electrical (电气特性):

Rated Current & Voltage: DC 12V;5A (额定电压&电流: 直流12V,5A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4. Insulation Resistance: 1,000MΩ minimum. (绝缘电阻: 1,000MΩ 以上)

Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)

5. WorkTemperture (工作环境):

Withstanding Higt Temperature: 280℃

Operational Temperature: - 20℃ ~ + 70℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm
SHEET:	1 of 1	PROJECTION	
DATE:	2020.08.03	VER.	D.0

THE UNMARKED TOLERANCE ARE AS BELOW :			
LENGTH		ANGLE	
X.XX	±0.05mm	X.XX	±0.50°
X.X	±0.10mm	X.X	±1.00°
X.	±0.20mm	X.	±2.00°

DESIGNED BY:		DWG. NO.	YZ49015045T-07025-01
CHECKED BY:		TITLE:	Pogo pin 连接器
APPROVED BY:			