







技术要求:

- 1. 塑件材料: PA66 (UL-94V-0)
- 2. 接触件: 黄铜镀锡
- 3. 接触电阻: $\leq 20m\Omega$
- 4. 绝缘电阻: $\geq 1000M\Omega$
- 5. 额定电压: 250V AC DC
- 6. 额定电流: 3.0A AC DC
- 7. 耐压: 能承受 1000V AC/Minute
- 8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
- 9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
- 10. 铅和镉等六大有害物质含量要符合环保要求.



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
JXT-VH3.96-2PZZ-P11	2	3.96	7.92
JXT-VH3.96-3PZZ-P11	3	7.92	11.88
JXT-VH3.96-4PZZ-P11	4	11.88	15.84
JXT-VH3.96-5PZZ-P11	5	15.84	19.80
JXT-VH3.96-6PZZ-P11	6	19.80	23.76
JXT-VH3.96-7PZZ-P11	7	23.76	27.72
JXT-VH3.96-8PZZ-P11	8	27.72	31.68
JXT-VH3.96-9PZZ-P11	9	31.68	35.64
JXT-VH3.96-10PZZ-P11	10	35.64	39.60
...	...	...	...
JXT-VH3.96-20PZZ-P11	20	(20-1)x3.96	(20+1)x3.96

2	端子 Contact	黄铜	N*1	电镀（锡）：整个表面镀底镍 30u”MIN,再镀锡80u”MIN	
1	基座 Wafer	LCP (UL94V-0)	1	米色	
序号	名称	材料	数量	备注	
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.20	X.* ±10°	PART NO.		TITLE: VH3.96MM 直针 带扣	
.XX ±0.10	.X* ± 8°	JXT-VH3.96-NPZZ-P11			
.XXX ±0.05	.XX* ± 5°	DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —			SCALE N:A	SHEET 1/1