




- Note:
- 1: Material (材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
- 2: Plating (电镀):
Barrel: 3u' Au over 50~80u' Ni (针管: 镀金3u', 镍底50~80u'.)
Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)
Spring: No plated (弹簧: 不电镀)
- 3: Electrical (电气特性):
Rated Current & Voltage: DC 12V, 1A (额定电压&电流: 直流12V, 1A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
- 4: Mechanical (机械性能):
Force: 75g±20% at working height. (75g±20% 在工作高度)。
Durability: 10,000 cycles (min) (寿命: 10000次)
- 5: Work Temperature (工作环境):
Withstanding Hight Temperature: 280℃
Operational Temperature: -40℃~ +85℃

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL: 0755-28773277 FAX: 0755-28891353



SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.	YZ218220140D-01
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE		CHECKED BY:		TITLE:	Pogo Pin
DATE:	2024.09.26	VER.	D.0	X.XX ±0.05mm	X.XX ±0.50°	X.X ±0.10mm	X.X ±1.00°	APPROVED BY:			
				X. ±0.20mm	X. ±2.00°						