




SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



技术要求:

1. 塑件材料: PA66 (UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $\geq 100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
JXT-XH2.54-2PWZ-P11	2	2.50	7.50
JXT-XH2.54-3PWZ-P11	3	5.00	10.00
JXT-XH2.54-4PWZ-P11	4	7.50	12.50
JXT-XH2.54-5PWZ-P11	5	10.00	15.00
JXT-XH2.54-6PWZ-P11	6	12.50	17.50
JXT-XH2.54-7PWZ-P11	7	15.00	20.00
JXT-XH2.54-8PWZ-P11	8	17.50	22.50
JXT-XH2.54-9PWZ-P11	9	20.00	25.00
JXT-XH2.54-10PWZ-P11	10	22.50	27.50
JXT-XH2.54-11PWZ-P11	11	25.00	30.00
JXT-XH2.54-12PWZ-P11	12	27.50	32.50
JXT-XH2.54-13PWZ-P11	13	30.00	35.00
JXT-XH2.54-14PWZ-P11	14	32.50	37.50
JXT-XH2.54-15PWZ-P11	15	35.00	40.00
JXT-XH2.54-16PWZ-P11	16	37.50	42.50
JXT-XH2.54-17PWZ-P11	17	40.00	45.00
JXT-XH2.54-18PWZ-P11	18	42.50	47.50
JXT-XH2.54-19PWZ-P11	19	45.00	50.00
JXT-XH2.54-20PWZ-P11	20	47.50	52.50

2	端子 Contact	黄铜	N*1	电镀(锡): 整个表面镀底镍 30u"MIN, 再镀锡 80u"MIN
1	基座 Wafer	PA66 (UL94 V-0)	1	白色
序号	名称	材料	数量	备注

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.20	X.* ±10°	PART NO.		TITLE:	
.XX ±0.10	.X* ± 8°	JXT-XH2.54-NPWZ-P11		XH2.54MM 弯针	
.XXX ±0.05	.XX* ± 5°	DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —			SCALE	SHEET
				N:A	1/1