











REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Applicable Flat Cable

Part No	Pin	A	B	C
JXT-AFC10-FX2P-H20	2	1.00	3.10	6.90
JXT-AFC10-FX3P-H20	3	2.00	4.10	7.90
JXT-AFC10-FX4P-H20	4	3.00	5.10	8.90
JXT-AFC10-FX5P-H20	5	4.00	6.10	9.90
JXT-AFC10-FX6P-H20	6	5.00	7.10	10.90
JXT-AFC10-FX7P-H20	7	6.00	8.10	11.90
JXT-AFC10-FX8P-H20	8	7.00	9.10	12.90
JXT-AFC10-FX9P-H20	9	8.00	10.10	13.90
JXT-AFC10-FX10P-H20	10	9.00	11.10	14.90
.....		...		
JXT-AFC10-FX32P-H20	32	(32-1)*1.0	(32+1)*1.0+0.10	(32+6)*1.0-0.10



适用线路板(PCB LAYOUT)

序号	品名	材质
1	0.5前翻胶芯(H2.0)	LCP UL94V-0 本色
2	0.5前翻端子(H2.0)	铜合金/表面镀锡
3	0.5前翻后盖(H2.0)	LCP UL94V-0 黑色
4	0.5前翻焊片(H2.0)	铜合金/表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC/DC(等效).
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 500M\Omega$

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X°±5°	PART NO.	TITLE:		
.XX±0.20	.XX°±2°	JXT-AFC10-FXNP-H20	1.0 Pitch 前翻卧式下接 (H=2.0)		
.XXX±0.05	.XXX°±1°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				