








- 说明:
- 1. 特性:
 - 额定电压 :250V AC最大值
 - 额定电流 :最大3A
 - 接触阻抗 :30mΩ MAX.
 - 绝缘阻抗 :3000MΩ MIN. at 500V DC
 - 耐电压值 :250V AC RMS for 1Minute
 - 工作温度 : -45℃~+85℃
 - 2. 材料:
 - 胶 芯 : PBT rated
 - 端 子 : 铜合金
 - 外 壳 : 铁合金/铜合金/不锈钢
 - 前壳镀镍后壳镀锡/钝化



203A 25 F X X XX X
1 2 3 4 5 6 7

- 1. 系列编号:
 - 203A=DP头冲针光孔
- 2. PIN位区分:
 - 09=9PIN 15=15PIN 25=25PIN 37=37PIN 50=50PIN
- 3. 公母区分:
 - F=母 M=公
- 4. 塑胶类别区分:
 - 1=黑胶 2=黑胶阻燃 3=白胶 4=白胶阻燃
 - 5=蓝胶 6=蓝胶阻燃
- 5. 电镀区分:
 - A=半金锡 G=全金
- 6. 镀层厚度:
 - 00=0.6u-0.8u金 01=1u金 02=2u金.....
 - 备注: 如果产品是半金锡的00数字那些代表金的u数其余部分镀锡默认80u-110u
- 7. 外壳区分:
 - A=铁壳12H B=铁壳24H C=铁壳48H
 - D=铜壳 E=不锈钢钝化
 - F=不锈钢镀镍 G=铁壳镀金

UNLESS OTHERWISE SPECIFIED TOLERANCE			 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD		
ANG.	±5°				
0.	±0.5				
.0	±0.3				
.00	±0.2				
SCALE: AS SHOWED		UNIT:	mm		
DRAWN WAN		07/07/08		DRAWN NAME: DP25母光孔	
CHECKED CHEN		07/07/08			
APPROVED CHEN		07/07/08			
		SIZE	A4	REV.	A
		FILE NAME: 203A25FXXXXX			
PRODUCT NO. 203A25F4G01A					

A ECN-20130617001(WAN)

REV. DESCRIPTION

DATE

SIZE A4

REV. A

FILE NAME: 203A25FXXXXX