




| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |
|      |         |             |      |        |



NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.0
- 2.Voltage Rating: 50V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

| Part No             | Pin | A     | B     | C     |
|---------------------|-----|-------|-------|-------|
| JXT-SH1.0-2PLB-P43  | 2   | 1.00  | 4.35  | 2.60  |
| JXT-SH1.0-3PLB-P43  | 3   | 2.00  | 5.35  | 3.60  |
| JXT-SH1.0-4PLB-P43  | 4   | 3.00  | 6.35  | 4.60  |
| JXT-SH1.0-5PLB-P43  | 5   | 4.00  | 7.35  | 5.60  |
| JXT-SH1.0-6PLB-P43  | 6   | 5.00  | 8.35  | 6.60  |
| JXT-SH1.0-7PLB-P43  | 7   | 6.00  | 9.35  | 7.60  |
| JXT-SH1.0-8PLB-P43  | 8   | 7.00  | 10.35 | 8.60  |
| JXT-SH1.0-9PLB-P43  | 9   | 8.00  | 11.35 | 9.60  |
| JXT-SH1.0-10PLB-P43 | 10  | 9.00  | 12.35 | 10.60 |
| JXT-SH1.0-11PLB-P43 | 11  | 10.00 | 13.35 | 11.60 |
| JXT-SH1.0-12PLB-P43 | 12  | 11.00 | 14.35 | 12.60 |
| JXT-SH1.0-13PLB-P43 | 13  | 12.00 | 15.35 | 13.60 |
| JXT-SH1.0-14PLB-P43 | 14  | 13.00 | 16.35 | 14.60 |
| JXT-SH1.0-15PLB-P43 | 15  | 14.00 | 17.35 | 15.60 |
| JXT-SH1.0-16PLB-P43 | 16  | 15.00 | 18.35 | 16.60 |
| JXT-SH1.0-20PLB-P43 | 20  | 19.00 | 22.35 | 20.60 |



| TOLERANCE  |           | 深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                         |              |
|------------|-----------|--------------------------------------------------------------------|-------------------------|--------------|
| X.X ±0.30  | X.* ±5°   | PART NO.<br>JXT-SH1.0-NPLB-P43                                     | TITLE:<br>WAFER 1.00 立贴 |              |
| .XX ±0.20  | X.X* ±3°  |                                                                    | MANUFACTURE DWG         |              |
| .XXX ±0.10 | X.XX* ±1° |                                                                    |                         |              |
| UNITS      | mm        | DESIGN:                                                            | Ethan                   |              |
| MATERILA   | ---       | CHED:                                                              | Olvia                   |              |
| FINISH     | ---       | APPD:                                                              | Ava                     |              |
|            |           |                                                                    |                         | SCALE<br>N:A |
|            |           |                                                                    |                         | SHEET<br>1/1 |