




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



- 技术要求:
1. 塑件材料:PA66(UL-94V-0)
 2. 接触件:黄铜镀锡
 3. 接触电阻:≤10mΩ
 4. 绝缘电阻:≥100MΩ
 5. 额定电压:250V AC DC
 6. 额定电流:2.0A AC DC
 7. 耐压:能承受1000V AC/Minute
 8. 工作温度:-25°~+85°
 9. 可焊性试验:浸锡面积≥95%温度235±5°, 时间2.5±0.5秒
 10. 铅和铜等六大有害物质含量要符合环保要求。

Part No	Pin	A	W	C
JXT-ZH1.5-2PWZ-P11	2	1.50	3.60	4.50
JXT-ZH1.5-3PWZ-P11	3	3.00	5.10	6.00
JXT-ZH1.5-4PWZ-P11	4	4.50	6.60	7.50
JXT-ZH1.5-5PWZ-P11	5	6.00	8.10	9.00
JXT-ZH1.5-6PWZ-P11	6	7.50	9.60	10.50
JXT-ZH1.5-7PWZ-P11	7	9.00	11.10	12.00
JXT-ZH1.5-8PWZ-P11	8	10.50	12.60	13.50
JXT-ZH1.5-9PWZ-P11	9	12.00	14.10	15.00
JXT-ZH1.5-10PWZ-P11	10	13.50	15.60	16.50
JXT-ZH1.5-11PWZ-P11	11	15.00	17.00	18.00
JXT-ZH1.5-12PWZ-P11	12	16.50	18.60	19.50
JXT-ZH1.5-13PWZ-P11	13	18.00	20.10	21.00
JXT-ZH1.5-14PWZ-P11	14	19.50	21.60	22.50
JXT-ZH1.5-15PWZ-P11	15	21.00	23.10	24.00
JXT-ZH1.5-16PWZ-P11	16	22.50	24.60	25.50



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

2	端子Contact	黄铜	N*1	电镀(锡):整个表面镀底镍 30u"MIN,再镀锡 80u"MIN
1	基座Wafer	PA66(UL94 V-0)	1	白色
序号	名称	材料	数量	备注

TOLERANCE

X.X ±0.20	X.* ±10°
.XX ±0.10	.X* ± 8°
.XXX ±0.05	.XX* ± 5°
UNITS	mm
MATERILA	---
FINISH	---

深圳聚兴泰电子科技有限公司
Shenzhen Juxingtai Electronic Technology Co., Ltd

PART NO.	TITLE:
JXT-ZH1.5-NPWZ-P11	ZH1.5MM 弯针
DESIGN: Ethan	MANUFACTURE DWG
CHED: Olvia	
APPD: Ava	

SCALE	SHEET
N:A	1/1