



| REV. | ECN NO. | DESCRIPTION | DATE | DESIGN |
|------|---------|-------------|------|--------|
|      |         |             |      |        |
|      |         |             |      |        |





NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC,DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

| Part No              | Pin | A     | B     | C     |
|----------------------|-----|-------|-------|-------|
| JXT-GH1.25-2PLB-P43  | 2   | 1.25  | 5.75  | 3.75  |
| JXT-GH1.25-3PLB-P43  | 3   | 2.50  | 7.00  | 5.00  |
| JXT-GH1.25-4PLB-P43  | 4   | 3.75  | 8.25  | 6.25  |
| JXT-GH1.25-5PLB-P43  | 5   | 5.00  | 9.50  | 7.50  |
| JXT-GH1.25-6PLB-P43  | 6   | 6.25  | 10.75 | 8.75  |
| JXT-GH1.25-7PLB-P43  | 7   | 7.50  | 12.00 | 10.00 |
| JXT-GH1.25-8PLB-P43  | 8   | 8.75  | 13.25 | 11.25 |
| JXT-GH1.25-9PLB-P43  | 9   | 10.00 | 14.50 | 12.50 |
| JXT-GH1.25-10PLB-P43 | 10  | 11.25 | 15.75 | 13.75 |
| JXT-GH1.25-11PLB-P43 | 11  | 12.50 | 17.00 | 15.00 |
| JXT-GH1.25-12PLB-P43 | 12  | 13.75 | 18.25 | 16.25 |
| JXT-GH1.25-13PLB-P43 | 13  | 15.00 | 19.50 | 17.50 |
| JXT-GH1.25-14PLB-P43 | 14  | 16.25 | 20.75 | 18.75 |
| JXT-GH1.25-15PLB-P43 | 15  | 17.50 | 22.00 | 20.00 |
| JXT-GH1.25-16PLB-P43 | 16  | 18.75 | 23.25 | 21.25 |



| TOLERANCE  |           | 深圳聚兴泰电子科技有限公司<br>Shenzhen Juxingtai Electronic Technology Co., Ltd |                   |       |
|------------|-----------|--------------------------------------------------------------------|-------------------|-------|
| X.X ±0.30  | X.* ±5°   | PART NO.                                                           | TITLE:            |       |
| .XX ±0.20  | X.X* ±3°  | JXT-GH1.25-NPLB-P43                                                | WAFER GH1.25 立贴带扣 |       |
| .XXX ±0.10 | X.XX* ±1° | DESIGN: Ethan                                                      | MANUFACTURE DWG   |       |
| UNITS      | mm        | CHED: Olvia                                                        |                   |       |
| MATERILA   | — — —     | APPD: Ava                                                          |                   |       |
| FINISH     | — — —     |                                                                    | SCALE             | SHEET |
|            |           |                                                                    | N:A               | 1/1   |