





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

P/N	PIN	DIM.A	DIM.B
JXT-PZ2.54-2X1P-A7	2*1	0.00	2.54
JXT-PZ2.54-2X2P-A7	2*2	2.54	5.08
JXT-PZ2.54-2X3P-A7	2*3	5.08	7.62
JXT-PZ2.54-2X4P-A7	2*4	7.62	10.16
JXT-PZ2.54-2X5P-A7	2*5	10.16	12.70
JXT-PZ2.54-2X6P-A7	2*6	12.70	15.24
JXT-PZ2.54-2X7P-A7	2*7	15.24	17.78
JXT-PZ2.54-2X8P-A7	2*8	17.78	20.32
JXT-PZ2.54-2X9P-A7	2*9	20.32	22.86
.....			
JXT-PZ2.54-2X40P-A7	2*40	(40-1)X2.54	(40)X2.54

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.* ±5°	PART NO.	TITLE: 2.54PH H2.5 2xPin 90度		
.XX ±0.20	X.X* ±1°	JXT-PZ2.54-2XNP-A7	PC3.0 PA6.0 PB6.9 L13.8/18.8		
.XXX ±0.10	X.XX* ±0.5°		6T 第四版		
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia		SCALE	SHEET
FINISH	— — —	APPD: Ava		N:A	1/1